

August 2024

Statement on EU REACH Directive

The Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) Regulation requires the identification of Substances of Very High Concern (SVHC) contained in articles above the threshold 0.1% w/w manufactured and marketed in the EU (Legal Reference EC 1907/2006).

In accordance with Article 33(1) of the REACH regulation, this communication applies to the below-referenced products included with this statement. Endress+Hauser products are manufactured in a way that the release of chemicals under normal and foreseeable circumstances does not take place.

Information is provided for all downstream users as soon as we become knowledgeable that our products consist of more than the above threshold.

See the table for the respective valid list: <https://echa.europa.eu/en/candidate-list-table>

Furthermore, the EU REACH Regulation restricts the manufacture, sale, or use, within the European Union, of substances listed in REACH Annex XVII. Restriction specifications and usage parameters are described in each substance's Annex XVII entry.

Endress+Hauser responsibly implements the restrictions of this list and, at the time of this declaration, does not manufacture or distribute any products containing substances from the currently valid REACH list of Annex XVII.

See the table for the respective valid list: <https://echa.europa.eu/en/substances-restricted-under-reach>

Endress+Hauser believes that the information it provides above is accurate. The information provided is based on data obtained from ongoing due diligence concerning goods and materials provided by third party suppliers. Endress+Hauser provides such information "AS IS", without any express or implied warranty of any kind. Endress+Hauser reserves the right to update and modify this communication, as it believes necessary or appropriate.



Michael Kanzinger
Trade Compliance Manager



Dr. Heiner Zehntner
General Counsel

Attachments:

- Recapitulation of the regulations of REACH
- Customer Information on REACH



Recapitulation of the regulations of REACH (EC Regulation 1907/2006)

1. REACH is a new European Union regulation concerning the Registration, Evaluation, Authorization and restriction of Chemicals. It came into force on 1st June 2007. A major part of REACH is the requirement for manufacturers or importers of substances to register them with a central [European Chemicals Agency \(EChA\)](#). REACH applies to substances manufactured or imported into the EU in quantities of 1 ton per year or more.
2. REACH requires [manufacturers and importers](#) of a [substance on its own or in a preparation](#) to communicate how their substances or preparations can be used safely for humans and environment. The main instrument for this communication down the supply chain is the [Safety Data Sheet](#) (SDS). The manufacturer, importer or downstream user will prepare the SDS according to a similar principle as he did before REACH came into force. The main difference is that when required, the SDS will also have an annex including [exposure scenarios](#) specifying the conditions under which the substance or preparation can be used safely, for uses that have been identified. The quality of the SDSs is expected to improve due to REACH as more information will be available because of the registration process.
3. Suppliers of [articles](#) shall inform their customers about substances of very high concern contained in concentrations above 0.1%. Also, consumers can request such information.
4. REACH requires all substances that are intended to be released from articles during normal and reasonably foreseeable conditions of use to be registered according to the normal rules, if they are produced or imported in quantities exceeding 1 ton/year per producer or importer. In addition, all substances included in the [candidate list](#) and which are present in articles above a concentration limit of 0.1% weight by weight and above 1 tons per year must be notified to the agency (EChA).
5. [Downstream users](#) have a right to make their use known to the supplier and in doing so have to provide sufficient information to prepare an exposure scenario. This upstream communication will play an important role when a registrant prepares a chemical safety report, including exposure scenarios if required, as a part of the registration dossier.

**Customer Information as per Art. 33 (1) of the REACH Directive EC No. 1907/2006
(To the current Candidate List of substances of very high concern for Authorization)**

The products listed below contain sub-products with an SVHC content of over 0.1 % w/w.

SVHC > 0.1 % w/w		CAS-No.
Lead Lead monoxide Lead titanium zirconium oxide Lead titanium trioxide		7439-92-1 1317-36-8 12626-81-2 12060-00-3
Products Description	Order Information	Component w. SVHC
	CYR52 CYM17 xPS64 / xPS65 xPK1 / 2 / 3 / 4 / 5 / 6 Kit COG30 Kit CSZ18 Kit V2A / V4A XPD0001-XPD00094	<ul style="list-style-type: none"> • Lead as constituents in, amongst other materials, aluminum, or copper alloys (brass). • Lead in high melting temperature type solders. • Lead in electronic devices and batteries. • Lead as radiation protection material for our Radiometric products.
ASP Station	RPx20B	
Bunker Metering Computer	SBC600	
Cerabar	PMC11 / 21 / 51 / 51B / 71 / 71B PMP11 / 21 / 23 / 51 / 51B / 55 / 71 / 71B	
Ceraliquid	xPS41 / xPS42 / xPS43 OPF41 / OPF42 / OPF43	
Ceraphant	PTC31B PTP31B / PTP33B	
Chemoclean	CYR10B	
Cleanfit	CPA474 / CPA473	
Cleanfit Control	CYC25	
CNGmass	8DF** 8FF** aD8CB**	
Conducal	CLY421	
Condumax	xLS12 / 13 / 15D / 19 / 21 / 21D / 52	
Commubox	FXA195 / FXA291	
Cubemass	8CM** 8CN** a8Cq**	
Deltabar	FMD71 / 72 / 77 / 78 PMD55 / 55B / 75 / 75B / 78B	
Deltapilot	FMB50 / 51 / 52 / 53 / 70	
Dipfit	CLA140	
Dosimag	5*H**	
Dosimass	8*E**	
Easytemp	TMR31 / TMR35	
EngyCal Energy Manager	RH33 / RS33 / RA33 RMC621 / RMS621	
Fermentation Monitor	QWX43	

FieldEdge	SGC200 / SGC400 / SGC500
Fieldgate	FXA42 SFG250 / SFG500 SWG50 / SWG70
Fieldport	SWA50 / SWA70 SFP20 / SFP50
Fieldbus Indicator	RID14 / RID16
Field Xpert	SMT50 / SMT70 / SMT77
FlowFit	CYA27
Flowphant T	DTT31 / DTT35
Gambro	6 / 7
Gammapilot	FMG50 / FMG60 FQG60 / 61 / 62 / 63 / 66 FTG20
Indicators	RIA14 / RIA15 / RIA16
Indumax	xLS54
Interfaces	RB223 RN221N / RN22 / RN42 RLN42 / RNF22 / RNO22 TID10
ISEmax	CAS40D
iTEMP Field Transmitter	TMT142 / TMT142B / TMT162
iTEMP Temperature Transmitters	TMT180 / 181 / 182B / 187 / 188 / 31 / 36 / 71 / 72 / 80 / 82 / 84 / 85 / 86 TMT111 / 112 / 121 / 122 / 127 / 128
iTHERM	TM101 / 111 / 121 / 131 / 151 / 311 TM401 / 402 / 411 / 412 TS111 / TS211 / TS212 TA30x TST434 / 434B
ITHERM MultiSens	TMS01 / 02 / 11 / 12 / 21 / 31
Levelflex	FMP50 / 51 / 52 / 53 / 54 / 55 / 56 / 57
Liquicap	FMI21 / FMI51 / FMI52 FTI51 / FTI52
Liquifloat	FTS20
Liquiline	CM42 CM44x OCM44x
Liquiline Compact	CM72 / 82
Liquiline control	CDC90
Liquiline to go	CYM291
Liquiline mobile	CML18
Liquiline System	CA80AM / COD / PH / TP / AL / HA / SI / TN / FE / CR / NO CAT810 CAZ800 / 820 / 860 / 880
Liquiphant	FTL31 / 33 / 41 / 50 / 50H / 51 / 51B / 51C / 51H / 62 / 64 / 70 / 71 / 80 / 81 / 85
Liquipoint	FTW23 / 31 / 32 / 33
Liquipoint	CSP44
Liquisis	CxM223 / CxM253 OxM253

See above.

Liquistation	CSF22 / 28 / 33 / 34 / 39 / 48
Liquitrend	QMW43
LNGmass	aD8LB
LPGmass	8FE** aD8EB**
Memobase Plus	CYZ71D
Memocheck	CYP02E
Memocheck Sim	CYP03D
Memosens	xLS21E xYK10 / xYK20 COS61
Micropilot	FMR10 / 20 / 50 / 51 / 52 / 53 / 532 / 54 / 540 / 56 / 57 / 60 / 62 / 67 FWR30 NMR81 / NMR84
Minicap	FTC260 / FTC262
Mycom	CCM141S
Modem	Viator Bluetooth MACTek Viator Power express
Norylab	xPS51 / xPS52 / xPS53 OPF51 / OPF52 / OPF53
Nivector	FTI26
Nivotester	FTC325 FTL325N / FTL325P / FTL825 FTR525 FTW325
Oil leak detector	NAR300
Overfill Prevention System	SOP300 / SOP600
Oxymax	COS22D / 51E761 / 61D / 80E
Panel and Field Meter	RIA45 / RIA46 / RIA452
Picomag	aDMA**
Process Transmitter	RMA42
Promag	a5bq*** 5pb** 10b**
Promass	a8cq*** 8pc** 40E**
Proservo	NMS80 / NMS81 / NMS83
Prosonic	FDU90 / 91 / 91F / 92 / 93 / 95 FMU30 / 40 / 41 / 42 / 44 / 90 / 95
Prosonic Flow	91W, 93P, 93T, 93W, 92F, 93C, 9P5B**, 9W4B**, 9I4B**, 9B2B**, 9G3B**, 9G5B**, 9E1B**, 9EHB**
Prowirl	7e2C**
Recorder – Data Manager	RSG35 / RSG45

See above.

RTD Thermometer	TR10 / 11 / 12 / 13 / 15 / 24 / 25 / 61 / 62 / 65 / 66 / 88 TST434 / TST602 / TST90 TET90
Samplefit	CSA420
Silopilot	FMM20 / FMM50
Smartec	CLD132 / CLD134 / CLD18
Smartsens	OPS31
Solicap	FTI55 / FTI56 / FTI77
Solimotion	FTR16 / FTR20
Soliphant	FTM20 / 21 / 50 / 51 / 52
Soliswitch	FTE20 / FTE30 / FTE31
Soliwave	FDR16 / FDR56 / FDR57 FQR16 / FQR56 / FQR57
Stabsonden	11362(Z) / 11363(Z) / 11375Z / 11961Z / 11371
Stamoclean	CAT221
Surge Arrester	HAW562 / HAW569
Tankvision	NXA20 / 820 / 821 / 822
Teqwave	aD9HB** / aD9FB** / aD9IB**
Thermocouple	TAF11 / 12D / 12S / 12T / 16 TC10 / 12 / 13 / 15 / 2 / 65 / 66 / 88 TSC310 TPC100 / TPC200 / TPC300
Thermophant	TTR31 / TTR35
TOC Analyzer	CA72TOC
Topclean	CPG30
TrustSens	TM371 / TM372
Turbimax	CUS50D / OCUS50D / CUS51D
t-mass	a6dA*** a6dq*** 65c**
Waterpilot	FMX11 / FMX21

See above.

Note: Lower case letters are to be seen as variables and complete the product root:

a = O, empty
b = D, E, H, L, P, S, W
c = A, E, F, G, H, I, K, O, P, Q, S,
d = A, B, F, I, T
e = D, F, O, R
f = F, H
g = B, E, G, I, W
h = D, E, L, P, S, W
p = 0, 1, 3, 4, 5
q = 1, 2, 3, 4, 5, 8, B
r = 1, 2, 3, 4, 5, H
x = C, O, OC

SVHC > 0.1 % w/w		CAS-No.	
Potassium Dichromate		7778-50-9	
Products Description	Order Information	Component w. SVHC	SVHC content
Reagent RB	CY80COD-CC+SD		8 %
Reagent COD2 (B)	CAY441-VxxAAE		2.1 %

SVHC > 0.1 % w/w		CAS-No.	
Di Sodium Tetraborate		1330-43-4	
Products Description	Order Information	Component w. SVHC	SVHC content
pH-buffer solution 9.00	CPY20-G		0.263 %
pH-buffer solution 9.22	CPY20-I		0.999 %

SVHC > 0.1 % w/w		CAS-No.	
Boric Acid		10043-35-3	
Products Description	Order Information	Component w. SVHC	SVHC content
pH-buffer solution 9.00	CPY20-G		0.107 %
pH-buffer solution 10.0	CPY20-K		0.332 %

SVHC > 0.1 % w/w		CAS-No.			
Octamethylcyclotetrasiloxane		556-67-2			
Products Description	Order Information	Component w. SVHC			
Liquiphant	FTL-	<ul style="list-style-type: none"> Sealing ring, 67,5x 2,9 / 1,5-VMQ/PTFE, only in combination with the F15 "hygienic" enclosure Gasket, profile 29x36x3.7, *SI-60 Gasket, profile 53x62x3,5, VMQ-60 Gasket, profile 125,5x139,5x 4,5, VMQ-60 Gasket, profile 141x161x5,5, VMQ-60 O-ring 30,0x2,00, VMQ-50 + PTFE Sealing cone d_i=7.5, SI 			
Soliphant	FTM-				
Cerabar	PMP- / PMC-				
Deltabar	FMD- / PMD-				
Deltapilot	FMB-				
Micropilot	FMR-				
Prosonic	FDU-				
Soliwave	FDR-				
Minicap	FTC-				
Solicap	FTI-				
Cleanfit	CPA871 / 875 XPC0001 / XPC0003			Silicone sealing ring	
Liquiline Control	CDC90				
Oil leak detector	NAR300				
Promass I	8I*B**				
Proservo	NMS8x	<ul style="list-style-type: none"> Silicone sealing ring 88,62 x 1,78 VMQ50(NMS80/81/83) 101,32 x 1,78 VMQ 50(NMS81) 59,4 x 3,1 VMQ 50(NMS80/81/83) 84,4 x 3,1 VMQ 50(NMS80/81/83) 119,40 x 3,1 VMQ 50 (NMS80) 158,34 x 3,53 VMQ 50 (NMS81/83) 			

SVHC > 0.1 % w/w		CAS-No.
Decamethylcyclopentasiloxane		541-02-6
Products Description	Order Information	Component w. SVHC
Liquiphant	FTL-	<ul style="list-style-type: none"> Sealing ring, 67,5x 2,9 / 1,5-VMQ/PTFE, only in combination with the F15 "hygienic" enclosure Gasket, profile 29x36x3.7, *SI-60 Gasket, profile 53x62x3,5, VMQ-60 Gasket, profile 125,5x139,5x 4,5, VMQ-60 Gasket, profile 141x161x5,5, VMQ-60 O-ring 30,0x2,00, VMQ-50 + PTFE Sealing cone d_i=7.5, SI
Soliphant	FTM-	
Cerabar	PMP- / PMC-	
Deltabar	FMD- / PMD-	
Deltapilot	FMB-	
Micropilot	FMR-	
Prosonic	FDU-	
Soliwave	FDR-	
Minicap	FTC-	
Solicap	FTI-	
Cleanfit	CPA871 / 875	Silicone sealing ring
Liquiline Control	CDC90	
Oil leak detector	NAR300	
Promass I	8I*B**	
Proservo	NMS8x	
		<ul style="list-style-type: none"> Silicone sealing ring 88,62 x 1,78 VMQ50(NMS80/81/83) 101,32 x 1,78 VMQ 50(NMS81) 59,4 x 3,1 VMQ 50(NMS80/81/83) 84,4 x 3,1 VMQ 50(NMS80/81/83) 119,40 x 3,1 VMQ 50 (NMS80) 158,34 x 3,53 VMQ 50 (NMS81/83)

SVHC > 0.1 % w/w		CAS-No.
Dodecamethylcyclohexasiloxane		540-97-6
Products Description	Order Information	Component w. SVHC
Liquiphant	FTL-	<ul style="list-style-type: none"> Sealing ring, 67,5x 2,9/ 1,5-VMQ/PTFE, only in combination with the F15 "hygienic" enclosure Gasket, profile 53x62x3,5, VMQ-60 Gasket, profile 125,5x139,5x 4,5, VMQ-60 Gasket, profile 141x161x5,5, VMQ-60 Sealing cone d_i=7.5, SI Ring, L-Zentrier- 29,7x31,5x9,8, VMQ-60 O-Ring 21,89x2,62, VMQ 70 + FDA, only in combination with the G1 adapter O-Ring 14,9x2,7, VMQ 75 + FDA, only in combination with the G3/4 adapter
Soliphant	FTM-	
Cerabar	PMP- / PMC-	
Deltabar	FMD- / PMD-	
Deltapilot	FMB-	
Micropilot	FMR-	
Prosonic	FDU-	
Soliwave	FDR-	
Minicap	FTC-	
Solicap	FTI-	
Liquicap	FMI-	
Liquipoint	FTW-	
Cleanfit	CPA871 / 875	
Liquiline Control	CDC90	
Oil leak detector	NAR300	
Promag W/P/L	5W / 5P / 5L****	Connector plug
Promass I	8I*B**	Silicone sealing ring

Proservo	NMS8x	<ul style="list-style-type: none"> • Silicone sealing ring • 88,62 x 1,78 VMQ50(NMS80/81/83) • 101,32 x 1,78 VMQ 50(NMS81) • 59,4 x 3,1 VMQ 50(NMS80/81/83) • 84,4 x 3,1 VMQ 50(NMS80/81/83) • 119,40 x 3,1 VMQ 50 (NMS80) • 158,34 x 3,53 VMQ 50 (NMS81/83)
----------	-------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

SVHC > 0.1 % w/w		CAS-No.
DOTE		15571-58-1
Products Description	Order Information	Component w. SVHC
Flowfit	CYA251 / CUA250 / COA250 / CYA21	PVC elements
Flexdip	CYA112	
Dipfit	CPA510 / CPA530	
Oxymax	COS61D	

SVHC > 0.1 % w/w		CAS-No.
Therphenyl - hydriert		61788-32-7
Products Description	Order Information	Component w. SVHC
Temperature sensor	CTS1	encapsulating materials

SVHC > 0.1 % w/w		CAS-No.
1,3-propanesultone		1120-71-4
Products Description	Order Information	Component w. SVHC
Liquiline Mobile	CML18	Prismatic Cell

SVHC > 0.1 % w/w		CAS-No.
1,2-dimethoxyethane, ethylene glycol dimethyl ether (EGDME)		110-71-4
Products Description	Order Information	Component w. SVHC
Memograph M	RSG45	Accu

SVHC > 0.1 % w/w		CAS-No.
Perfluorobutane sulfonic acid (PFBS) and its salts		---
Products Description	Order Information	Component w. SVHC
Liquisis	CxM221 / CxM223	Housing
Sampler	RPx20B	Electronic

SVHC > 0.1 % w/w		CAS-No.
Diboron trioxide		1303-86-2
Products Description	Order Information	Component w. SVHC
Liquiline	CM42	Electronic device
Liquiline Control	CDC90	
Liquiline System	CAT820	

SVHC > 0.1 % w/w		CAS-No.
Cadmium oxide		1306-19-0
Products Description	Order Information	Component w. SVHC
Prosonic	FMU-	Piezo disc
Liquiphant	FTL-	
Soliphant	FTM-	

SVHC > 0.1 % w/w		CAS-No.
1,3,5-Triazine-2,4,6-triamine		21840-08-4
Products Description	Order Information	Component w. SVHC
Promag	5hq***	Cable tree

SVHC > 0.1 % w/w		CAS-No.
Trilead bis(carbonate)dihydroxide		1319-46-6
Products Description	Order Information	Component w. SVHC
Panel Meter	RIA452	Electronic
Density calculator	FML621	
Energy manager	RMC621	

SVHC > 0.1 % w/w		CAS-No.
Bumetrizole		3896-11-5
Products Description	Order Information	Component w. SVHC
Promass	a8cq*** 8pc**	LCD Modul
t-mass	a6dA*** a6dq***	
Cleanfit	CPA450	Sealing insert
Indumax	xLS54	

SVHC > 0.1 % w/w		CAS-No.
Dicyclohexyl phthalate (DCHP)		84-61-7
Products Description	Order Information	Component w. SVHC
Ceraphant	PTP- / PTC-	Protect vent
Cerabar	PMC- / PMP-	

SVHC > 0.1 % w/w		CAS-No.
6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol		119-47-1
Products Description	Order Information	Component w. SVHC
Promass	a8cq*** 8pc** 40E**	Connector

CNGmass	8DF** 8FF** aD8CB**	
Cubemass	8CM** 8CN** a8Cq**	
t-mass	a6dA*** a6dq*** 65c**	
Indumax	OLS50	Shrinking tube
Smartec	CLD134	
TrustSens	TM371 TM372	
ASP Station	RPS20B	Various O-rings, gaskets and sealing rings from compound E7502
Cerabar	PMC11 / 21 / 51 / 51B / 71 / 71B PMP11 / 21 / 23 / 51 / 51B / 55 / 71 / 71B / 75	
Ceraliquid	xPS41 / xPS42 / xPS43	
Ceraphant	PTC31B PTP31B / PTP33B	
Chemoclean	xPR30	
Cleanfit	CPA450 / 472D / 473 / 474 / 475 / 871 / 875 XPC0001 / XPC0003	
Condumax	CLS12 / CLS15D xLS21D	
Deltabar	FMD77 / FMD78 / FMD78B PMD55 / 55B / 75 / 75B / 78B	
Deltapilot	FMB50 / 51 / 52 / 53 / 70	
Dipfit	CLA111 / CPA111	
Fermentation Monitor	QWX43	
Fieldport	SWA70	
Flowfit	xCA250 xOA250 / xOA260 CUA250 / CUA251 CYA251	
Gammapilot	FMG60 FQG61 / FQG62 FTG20	
Levelflex	FMP 50 / 51 / 52 / 53 / 54 / 55 / 56 / 57	
Liquicap	FMI21 / FMI51 / FMI52 FTI51 / FTI52	
Liquiline Control	CDC90	

Liquiline System	CA80COD / TP CAV800
Liquiphant	FTL31 / 33 / 41 / 50 / 50H / 51 / 51B / 51C / 51H / 62 / 63 / 64 / 70 / 71 / 80 / 81 / 85
Liquipoint	FTW23 / 31 / 32 / 33
Liquiport	CSP44
Liquistation	CSF28 / 34 / 39 / 48
Liquitrend	QMW43
Memosens	CLS15E / 21E xLS82E xOS22E / xOS22Z COS81D / xOS81E COL37E xOV81 CPS16D / 16E
Micropilot	FMR43 / 50 / 51 / 52 / 53 / 532 / 54 / 540 / 56/57/60/62/67 NMR81 / NMR84
Minicap	FTC260 / FTC262
Nivector	FTI26
Oil leak detector	NAR300
Orbisint	xPS11 / 12
Oxymax	COS22 / 41 / 61D
Proservo	NMS80 / NMS81 / NMS83
Prosonic	FDU90 FMU30 / 40 / 41 / 42 / 44
Remote Display	FHX50
Samplefit	CSA420
Solicap	FTI55 / FTI56 / FTI77
Soliphant	FTM20 / 21 / 50 / 51 / 52
Tankside Monitor	NRF81
Transducer	UC- 3/3B
Turbimax	CUS51D
Unifit	CPA442 / 842
Viomax	CAS51D

